







<b>l3</b>	<b>l4</b>	<b>l5</b>	<b>d3</b>	<b>d1</b>	<b>d2</b>	<b>l1</b>	<b>l2</b>	<b>Nr. / No.</b>	<b>d2</b>	<b>Nr. / No.</b>
10	10	12	71	66	50	136	155	E 1000/50 - 136/155	52	E 1000/52 - 136/155
							195	E 1000/50 - 136/195		E 1000/52 - 136/195
						156	135	E 1000/50 - 156/135		E 1000/52 - 156/135
							155	E 1000/50 - 156/155		E 1000/52 - 156/155
							195	E 1000/50 - 156/195		E 1000/52 - 156/195
						176	155	E 1000/50 - 176/155		E 1000/52 - 176/155
							195	E 1000/50 - 176/195		E 1000/52 - 176/195
							235	E 1000/50 - 176/235		E 1000/52 - 176/235
						196	155	E 1000/50 - 196/155		E 1000/52 - 196/155
							195	E 1000/50 - 196/195		E 1000/52 - 196/195
							235	E 1000/50 - 196/235		E 1000/52 - 196/235
						216	155	E 1000/50 - 216/155		E 1000/52 - 216/155
							195	E 1000/50 - 216/195		E 1000/52 - 216/195
							235	E 1000/50 - 216/235		E 1000/52 - 216/235
						236	155	E 1000/50 - 236/155		E 1000/52 - 236/155
							195	E 1000/50 - 236/195		E 1000/52 - 236/195
							235	E 1000/50 - 236/235		E 1000/52 - 236/235
							275	E 1000/50 - 236/275		E 1000/52 - 236/275
						256	155	E 1000/50 - 256/155		E 1000/52 - 256/155
							195	E 1000/50 - 256/195		E 1000/52 - 256/195
							235	E 1000/50 - 256/235		E 1000/52 - 256/235
							275	E 1000/50 - 256/275		E 1000/52 - 256/275