


E 1250



Druckstück gefedert ohne Bund

Spring-loaded thrust piece without collar



Mat.: 1.0715

t max. = 350°C

F1 [N]	F2 [N]	l1	l2	d2	d1	Nr. / No.
2	3	7	0.5	1.5	M 3	E 1250/ 3
4	10	9	0.8	2.5	M 4	E 1250/ 4
6	11	12	0.9	3	M 5	E 1250/ 5
9	15	14	1	3.5	M 6	E 1250/ 6
18	30	16	1.5	5	M 8	E 1250/ 8
20	40	19	2	6	M10	E 1250/10
30	55	22	2.5	8	M12	E 1250/12
65	120	24	3.5	10	M16	E 1250/16
90	140	30	4.5	12	M20	E 1250/20