

## E 1512




### Stützbolzen mit Führungsdurchmesser abgesetzt

Support pillar with guiding diameter, offset

» Für Auswerferpaketführung


» For ejector set guiding



Mat.: 1.1213      ≈ 60 HRC

M	h1	d2	d1	l	Nr. / No.
M 8	7	14	24	36	E 1512/24x 36
				46	E 1512/24x 46
				56	E 1512/24x 56
				66	E 1512/24x 66
				76	E 1512/24x 76
				86	E 1512/24x 86
				96	E 1512/24x 96
M10	9	18	36	116	E 1512/24x116
				46	E 1512/36x 46
				56	E 1512/36x 56
				66	E 1512/36x 66
				76	E 1512/36x 76
				86	E 1512/36x 86
				96	E 1512/36x 96
M12	10	20	48	116	E 1512/36x116
				136	E 1512/36x136
				46	E 1512/48x 46
				56	E 1512/48x 56
				66	E 1512/48x 66
				76	E 1512/48x 76
				86	E 1512/48x 86
				96	E 1512/48x 96
				116	E 1512/48x116
				136	E 1512/48x136
				156	E 1512/48x156

Einbauvariante 1  
Types of installation 1



Einbauvariante 2  
Types of installation 2

Wärmeausdehnungsunterschiede beachten!  
Observe differences in thermal expansion

