


**E 2751**



**Thermofühlerkabel**

*Thermocouple cable*



t max. = 70 °C

Zonen / Zones	d	Adernanzahl / Number of cores	l [m]	Nr. / No.
12	13.8	24 x 0.5	10	E 2751/24/10
			40	E 2751/24/40

» 0,5 mm<sup>2</sup> FeCuNi, Typ J (DIN EN 60584)

» paarweise nummeriert 1–12

» numbered in pairs 1–12

» schwarz+/weiß–

» black+/white–

» Ummantelung: PVC

» Sheath: PVC