





E 3240



## Schrägauswerferinheit

Inclined ejection unit



3.2

Mat.: 1.2344 ≈ 60 HRC

Hub1 max. / Stroke1 max.	r1	s1	d2	l2	s2	b3	s3 <sup>1)</sup>	r3	b4	l4	s4	b5	s5	b1	l1	Nr. / No.
16	2.5	6	M4	20	13	4	8	12	15.9	14	21	6.6	4	16	33	E 3240/16/33
12	5		M5			6.1	12	10	21.5	18	25	11.5	5	22	33	E 3240/22/33
30				30											52	E 3240/22/52

- 1) s3: Mit Zugabe zum Abstimmen / s3: With allowance for adjusting
- 2) W: Winkel stufenlos bis max. 10° / W: Angle floating up to max. 10°

