



PSG

PRODUCT DESCRIPTION

- » Highest process security and reliable temperature regulation through state-of-the-art hardware and software components
- » Ergonomic and intuitive operation with multi-touch screen
- » Compact design for minimal space requirements
- » High-end features such as intelligent power regulation, MoldCheck, and much more



L	B	H	Wt.	CEE mains connection	Digital inputs/ outputs	Maximum output	Number of zones	Pin assignment	No.	EUR
260	390	400	21 kg	16 A	2 / 1	11 kW	6	PSG	profiTEMP+/ 6/PSG	<>
260	390	400	22 kg	32 A	2 / 1	22 kW	12	PSG	profiTEMP+/12/PSG	<>
260	390	400	23 kg	63 A	2 / 1	43 kW	18	PSG	profiTEMP+/18/PSG	<>
260	390	400	24 kg	63 A	2 / 1	43 kW	24	PSG	profiTEMP+/24/PSG	<>
450	390	400	32 kg	63 A	2 / 1	43 kW	36	PSG	profiTEMP+/36/PSG	<>
450	390	400	34 kg	63 A	2 / 1	43 kW	48	PSG	profiTEMP+/48/PSG	<>
260	390	400	21 kg	16 A	2 / 1	11 kW	6	121	profiTEMP+/ 6/121	<>
260	390	400	22 kg	32 A	2 / 1	22 kW	12	121	profiTEMP+/12/121	<>
260	390	400	23 kg	63 A	2 / 1	43 kW	18	121	profiTEMP+/18/121	<>
260	390	400	24 kg	63 A	2 / 1	43 kW	24	121	profiTEMP+/24/121	<>
260	390	400	21 kg	16 A	2 / 1	11 kW	6	522	profiTEMP+/ 6/522	<>
260	390	400	22 kg	32 A	2 / 1	22 kW	12	522	profiTEMP+/12/522	<>
260	390	400	23 kg	63 A	2 / 1	43 kW	18	522	profiTEMP+/18/522	<>
260	390	400	24 kg	63 A	2 / 1	43 kW	24	522	profiTEMP+/24/522	<>
260	390	400	21 kg	16 A	2 / 1	11 kW	6	620	profiTEMP+/ 6/620	<>
260	390	400	22 kg	32 A	2 / 1	22 kW	12	620	profiTEMP+/12/620	<>
260	390	400	23 kg	63 A	2 / 1	43 kW	18	620	profiTEMP+/18/620	<>
260	390	400	24 kg	63 A	2 / 1	43 kW	24	620	profiTEMP+/24/620	<>

SPECIAL DESIGNS AVAILABLE:

Pin assignment: special pin assignment possible on request

For custom-made products or specific questions, simply contact Meusburger for professional specialist advice

