


PRODUCT DESCRIPTION

» Suitable for profiTEMP+ and profiTEMP TM



d	l	Type	 Pcs. / PU	No.	EUR
6	32	500VAC/16A/FF	10	RHZ 5000/ 500/ 16/FF	< >