







ÜBERSICHT SCHIEBERSICHERUNG OVERVIEW SLIDE RETAINERS

Schiebersicherung Slide retainer	Halteplatte Retainer plate	Abmessungen Dimensions	Haltekraft [N] Locking force [N]	max. Temp.	mit Rolle with roll
E 3051		48x14	60 100 140	200 °C	✓
E 3040		38x16 48x20 57x24	100 140 180	145 °C	✓
E 3042	E 3043 	∅16 ... ∅28	10 ... 340	220 °C	✓
E 3044	E 3045 	30x12 38x16 50x20	28 38 44	180 °C	-
E 3046	E 3047 	∅13 ∅18 ∅27	28 34 58	180 °C	-
E 3048	E 3049 	53x18	98	180 °C	-

Kugeldruckstück Ball catch	Abmessungen Dimensions	Federkraft Spring force		max. Temp.	mit Rolle with roll
		F1 [N]	F2 [N]		
E 1250	M3 ... M20	2 ... 90	3 ... 140	350 °C	-
E 1251	M3 ... M16	2 ... 65	3 ... 125	350 °C	-
E 1252	M3 ... M20	5 ... 115	7 ... 240	350 °C	-
E 1260	M4 ... M12	6 ... 35	12 ... 60	350 °C	-
E 1265	∅4 ... ∅12	2.5 ... 12	6 ... 26.5	250 °C	-

Haltekraft/Federkraft [N]
Locking force/Spring force [N]

