


E 5226



Kugelkäfig mit Fallsicherung

Ball cage with retaining ring



Mat.: 1.3505 / Aluminium

d4	d3	nk ¹⁾	d2	l	Nr. / No.			
16	2	72	12	20	E 5226/12 x 20			
		84		25	E 5226/12 x 25			
		108		30	E 5226/12 x 30			
		132		36	E 5226/12 x 36			
		156		45	E 5226/12 x 45			
		192		56	E 5226/12 x 56			
21	3	72	15	30	E 5226/15 x 30			
22	3	48	16	25	E 5226/16 x 25			
		72		30	E 5226/16 x 30			
		84		36	E 5226/16 x 36			
		108		45	E 5226/16 x 45			
		144		56	E 5226/16 x 56			
		96		30	E 5226/19 x 30			
25	3	112	19	36	E 5226/19 x 36			
		160		45	E 5226/19 x 45			
		208		56	E 5226/19 x 56			
		272		71	E 5226/19 x 71			
		96		30	E 5226/20 x 30			
		26		3	128	20	36	E 5226/20 x 36
160	45		E 5226/20 x 45					
208	56		E 5226/20 x 56					
272	71		E 5226/20 x 71					
304	80		E 5226/20 x 80					
144	36		E 5226/24 x 36					
234	56		E 5226/24 x 56					
108	30		E 5226/25 x 30					
31	3	144	25	36	E 5226/25 x 36			
		180		45	E 5226/25 x 45			
		234		56	E 5226/25 x 56			
		306		71	E 5226/25 x 71			
		342		80	E 5226/25 x 80			
		414		95	E 5226/25 x 95			
		102		36	E 5226/32 x 36			
		40		4	136	32	45	E 5226/32 x 45
170	56		E 5226/32 x 56					
204	63		E 5226/32 x 63					
238	71		E 5226/32 x 71					
272	80		E 5226/32 x 80					
306	95		E 5226/32 x 95					
425	120		E 5226/32 x 120					
160	45		E 5226/40 x 45					
48	4		200		40		56	E 5226/40 x 56
			240				63	E 5226/40 x 63
		280	71	E 5226/40 x 71				
		320	80	E 5226/40 x 80				
		380	95	E 5226/40 x 95				
		500	120	E 5226/40 x 120				
		580	140	E 5226/40 x 140				
		240	56	E 5226/50 x 56				
		58	4	288		50	63	E 5226/50 x 63
				384			80	E 5226/50 x 80
456	95			E 5226/50 x 95				
600	120			E 5226/50 x 120				
696	140			E 5226/50 x 140				
792	160			E 5226/50 x 160				
496	80			E 5226/63 x 80				
71	4	558	63	95	E 5226/63 x 95			
		775		120	E 5226/63 x 120			
		899		140	E 5226/63 x 140			
		1023		160	E 5226/63 x 160			

1) nk: Anzahl Stahlkugeln / nk: number of steel balls



