


E 1556



Elastomerdruckfeder, 70 Shore A

Elastomer compression spring, 70 Shore A



Mat.: CR (70 Shore A)

DIN ISO 10069-1

t max = 80°C

Fn [N]	Sn¹⁾	d1f	d2	d1	Lo	Nr. / No.			
460	5	23	6.5	16	12	E 1556/ 16 x 12			
450	6.4				16	E 1556/ 16 x 16			
435	8				20	E 1556/ 16 x 20			
	9.9				25	E 1556/ 16 x 25			
670	6.5	29	8.5	20	16	E 1556/ 20 x 16			
650	8				20	E 1556/ 20 x 20			
615	10.1				25	E 1556/ 20 x 25			
595	12.8				32	E 1556/ 20 x 32			
1000	7.8	36	10.5	25	20	E 1556/ 25 x 20			
930	9.9				25	E 1556/ 25 x 25			
920	12.8				32	E 1556/ 25 x 32			
970	15.9				40	E 1556/ 25 x 40			
2500	13.5	47	13.5	32	32	E 1556/ 32 x 32			
2600	16.3				40	E 1556/ 32 x 40			
2550	20.2				50	E 1556/ 32 x 50			
2450	25.6				63	E 1556/ 32 x 63			
4600	13.5	59	13.5	40	32	E 1556/ 40 x 32			
4400	16.8				40	E 1556/ 40 x 40			
4250	20.5				50	E 1556/ 40 x 50			
	26.3				63	E 1556/ 40 x 63			
4200	32	72	17	50	80	E 1556/ 40 x 80			
8100	13				32	E 1556/ 50 x 32			
7800	16				40	E 1556/ 50 x 40			
7500	20				50	E 1556/ 50 x 50			
7200	25.5	92	17	63	63	E 1556/ 50 x 63			
7000	32				80	E 1556/ 50 x 80			
7100	40				100	E 1556/ 50 x 100			
13900	13				32	E 1556/ 63 x 32			
13500	17	92	17	63	40	E 1556/ 63 x 40			
13300	21				50	E 1556/ 63 x 50			
13000	25				63	E 1556/ 63 x 63			
	32				80	E 1556/ 63 x 80			
12800	40	92	17	63	100	E 1556/ 63 x 100			
	50				125	E 1556/ 63 x 125			
21000	13				117	21	80	32	E 1556/ 80 x 32
20500	17							40	E 1556/ 80 x 40
20000	20	50	E 1556/ 80 x 50						
19700	26	63	E 1556/ 80 x 63						
19500	32	117	21	80	80	E 1556/ 80 x 80			
19300	40				100	E 1556/ 80 x 100			
20000	50				125	E 1556/ 80 x 125			

1) Sn: Max. zulässiger Federweg / Sn: maximum permissible travel

i 1 N = 0.1 daN = 0.102 kg



