


PRODUKTBESCHREIBUNG

- » Bis M12 Festigkeitsklasse 10.9
- » Ab M16 Festigkeitsklasse 8.8



b	b2	l2	M	b1	l	Nr.	EUR
13	7,7	35	M 8	8	50	HWS 9010/ 8/ 8/ 50	< >
15	9,7	30	M10	10	40	HWS 9010/10/10/ 40	< >
15	9,7	45	M10	10	63	HWS 9010/10/10/ 63	< >
15	9,7	50	M10	10	80	HWS 9010/10/10/ 80	< >
15	9,7	60	M10	10	100	HWS 9010/10/10/100	< >
18	11,7	35	M12	12	50	HWS 9010/12/12/ 50	< >
18	11,7	40	M12	12	63	HWS 9010/12/12/ 63	< >
18	11,7	55	M12	12	80	HWS 9010/12/12/ 80	< >
18	11,7	65	M12	12	100	HWS 9010/12/12/100	< >
22	13,7	35	M12	14	50	HWS 9010/12/14/ 50	< >
22	13,7	45	M12	14	63	HWS 9010/12/14/ 63	< >
22	13,7	55	M12	14	80	HWS 9010/12/14/ 80	< >
22	13,7	65	M12	14	100	HWS 9010/12/14/100	< >
22	13,7	75	M12	14	125	HWS 9010/12/14/125	< >
25	15,7	45	M16	16	63	HWS 9010/16/16/ 63	< >
25	15,7	55	M16	16	80	HWS 9010/16/16/ 80	< >
25	15,7	65	M16	16	100	HWS 9010/16/16/100	< >

b	b2	l2	M	b1	l	Nr.	EUR
25	15,7	85	M16	16	125	HWS 9010/16/16/125	< >
25	15,7	100	M16	16	160	HWS 9010/16/16/160	< >
25	15,7	125	M16	16	200	HWS 9010/16/16/200	< >
28	17,7	45	M16	18	63	HWS 9010/16/18/ 63	< >
28	17,7	55	M16	18	80	HWS 9010/16/18/ 80	< >
28	17,7	65	M16	18	100	HWS 9010/16/18/100	< >
28	17,7	85	M16	18	125	HWS 9010/16/18/125	< >
28	17,7	100	M16	18	160	HWS 9010/16/18/160	< >
32	19,7	65	M20	20	100	HWS 9010/20/20/100	< >
32	19,7	85	M20	20	125	HWS 9010/20/20/125	< >
32	19,7	110	M20	20	160	HWS 9010/20/20/160	< >
32	19,7	125	M20	20	200	HWS 9010/20/20/200	< >
35	21,7	65	M20	22	100	HWS 9010/20/22/100	< >
35	21,7	85	M20	22	125	HWS 9010/20/22/125	< >
35	21,7	110	M20	22	160	HWS 9010/20/22/160	< >
35	21,7	125	M20	22	200	HWS 9010/20/22/200	< >